Electric Terminal Unit Actuator

Product Bulletin

PB_VA-748x_01 2021 January 2021

Overview

The VA-748x Series Electric Terminal Unit Valve Actuator provides floating, proportional, or proportional control with 0-10V position feedback signal and electric fail safe function in HVAC applications. The compact design of this actuator series makes it suitable for installation in confined locations, such as fan coils, chilled ceilings, manifolds, and more.

The VA-748x Series Actuator is designed for field mounting onto Johnson Controls and competitors' terminal unit valves. Due to the innovative concept of auto stroke detection, the VA-748x can be installed over most of the conventional terminal unit valves and pressure independent control valves (PICV) with variable strokes on the market.



Figure 1: VA-748x Series Electric Terminal Unit Actuator

Features

- Low and line voltage Flexible applications
- Floating and proportional control Flexible applications
- · Voltage and current analog input Suitable for any controller
- · Different analog input ranges Flexible applications
- Different actuator speeds New market opportunities
- · Double and RGB colour LED Provide information about status and diagnostic
- Removable cable No expert required for connection or replacement
- Different cable length available as separate kit OEM's version easily available
- · Auto stroke detection Suitable for valve with variable stroke
- Feedback control 0-10 VDC with max. 2mA output current
- Electrical fail safe Protects the equipment and the system from damage, while enhancing overall efficiency

Ordering codes

Product codes	Control type	Power supply	Running time	Nominal force	Factory stroke config.	Cable length	Mounting thread nut	Special config.	Feedback	Electrical fail safe	Enclo- sure							
VA-7480-0011						1.5 m												
VA-7480-0312			13 sec/mm			3m	M28x1.5	UL Listed										
VA-7481-0011			8 sec/mm	120 N					1									
VA-7480-0001		24 VAC	13 sec/mm]		1.5 m												
VA-7481-0001		24 VAC	8 sec/mm								IP54							
VA-7480-0201-TA				140 N		2 m	M30x1.5											
VA-7480-0501-TA	Floating					5 m												
VA-7480-4001			13 sec/mm															
VA-7480-4003																		
VA-7480-0013	-						M28x1.5											
VA-7481-0013	-	230 VAC	8 sec/mm	120 N		1.5 m					IP43							
VA-7480-0003 VA-7481-0003			13 sec/mm	-			M20v4 F											
VA-7481-0003 VA-7481-4003			8 sec/mm				M30x1.5											
VA-7481-4003					3.2 mm													
VA-7482-2001					4.3 mm													
VA-7482-2001 VA-7482-3001					6.0 mm	1.5 m												
VA-7482-3001 VA-7482-1001-RA					0.0 mm		M30x1.5		-									
VA-7482-1301-RA			120 N	120 N	3.2 mm	3 m	-	Reverse action										
VA-7482-2001-RA					4.3 mm													
VA-7482-0011						1.5 m			1									
VA-7482-0311							M28x1.5											
VA-7482-0312	-					3 m		UL Listed]									
VA-7482-2201-TA											2 m		Reverse	1				
VA-7482-2501-TA											140 N	4.3 mm	5 m		action			
VA-7482-5001											2.5 mm		1		1		l	
VA-7482-6001				120 N	5 mm	1.5 m												
VA-7482-7001					5.5 mm													
VA-7482-8201	Proportional	24 VAC/	8 sec/mm								IP54							
VA-7482-9201	Поронаона	VDC	0 360/1111			2 m halogen					11 04							
VA-7482-8201-RA						free		Reverse										
VA-7482-9201-RA								action										
VA-7482-8002-RA						1.5 m		Reverse										
VA-7482-9002-RA						CMP	M30x1.5	action and										
VA-7482-8302-RA						3 m CMP		UL listed										
VA-7483-8201			160 N	160 N	Auto stroke detection													
VA-7483-9201						2 m halogen												
VA-7483-8201-RA						free		Reverse										
VA-7483-9201-RA								action										
VA-7484-8001									•									
VA-7484-9001						1.5 m												
VA-7484-8001-RA						halogen free		Povoras	1	•								
VA-7484-9001-RA								Reverse action										

Accessories (order separately)

Accessories codes	Description	Packing
VA-7480-CAB21	Floating 24V – 2 m length	
VA-7480-CAB31	Floating 24V – 3 m length	
VA-7480-CAB51	Floating 24V – 5 m length	
VA-7480-CAB11	Floating 24V – 10 m length	
VA-7480-CAB33	Floating 230V – 3 m length	
VA-7480-CAB53	Floating 230V – 5 m length	
VA-7480-CAB73	Floating 230V – 7 m length	Diactic Rog
VA-7480-CAB13	Floating 230V – 10 m length	Plastic Bag
VA-7482-CAB21	Proportional 24V – 2 m length	
VA-7482-CAB31	Proportional 24V – 3 m length	
VA-7482-CAB51	Proportional 24V – 5 m length	
VA-7482-CAB71-HF	Proportional 24V – 7 m length - Halogen free	
VA-7482-CAB21-HF	Proportional 24V – 2 m length - Halogen free	
VA-7482CAB7452	Cable kit to replace VA-7452 with VA-7482	
VA-748X-CONF	Configuration tool Single pack	Single pack

Valve compatibility (1/2)

Actuator codes	Johnson Controls	Danfoss	Frese	Industrie Technik	Oventrop	Sauter	Schneider Electric	Siemens	TA Hydronics	Fratelli Pettinaroli	Watts Industries	Controlli		
VA-7480-0011														
VA-7480-0312														
VA-7481-0011	VG4000 Series													
VA-7480-0013	(discontinued)													
VA-7481-0013	VG5000 Series													
VA-7482-0011	(discontinued)													
VA-7482-0311														
VA-7482-0312														
VA-7480-0001						VUL Series								
VA-7481-0001	VG3000 Series V5000 Series (discontinued) VG6000 Series (discontinued)	AB-QM (DN15-DN32)		VFX (DN15-DN20)	COCON QTZ (DN10-DN32) COCON 2TZ (DN15-DN20) Tri-M Plus	BUL Series VUT Series BUT Series VXL Series	VZx8 Series VZx8C (DN15-DN20)	VVP47 Series VXP47 Series VMP47 Series VVI46 Series VXI46 Series	TA Compact (DN10-DN32) TA Modulator (DN15-DN20)	91 Series 92 Series 93 Series	2131 Series 3131 Series 4131 Series			
VA-7480-0003	VP1000 Series						(DN15)	BXL Series VCL (DN10-DN32)		VVS46 Series VXS46 Series				
VA-7481-0003								VVP47 Series						
VA-7482-1001 VA-7482-1001-RA VA-7482-1301-RA	VP1000 (DN15-DN20) VG6000 Series (discontinued)	AB-QM (DN10-DN20)		VFX Series (DN15-DN20)	COCON QTZ (DN10-DN15)	VUT Series BUT Series VXL Series BXL Series VCL (DN10-DN15)	VZx8 Series VZx8C (DN15-DN20)	VXP47 Series VMP47 Series VVI46 Series VXI46 Series VVS46 Series VXS46 Series		91 Series	2131 Series 3131 Series 4131 Series			
VA-7482-2001 VA-7482-2001-RA	VG3000 Series V5000 Series (discontinued)				COCON QTZ (DN20-DN32) COCON 2TZ (DN15-DN20) Tri-M Plus (DN15)	VUL Series BUL Series VCL (DN20-DN32)								
VA-7482-3001	VP1000 (DN25-DN32)	AB-QM (DN25-DN32)								93 Series				
VA-7480-0201-TA VA-7480-0501-TA									TBV-C (DN15-DN25) TBV-CM (DN15-DN25) TBV-CMP (DN15-DN25) KTCM512 (DN15-DN25)					
VA-7482-2201-TA VA-7482-2501-TA									TBV-C (DN15-DN20) TBV-CM (DN15- DN25) TBV-CMP (DN15-DN25) KTCM512 (DN15-DN25)					

Valve compatibility (2/2) Fratelli Pettinaroli TA Hydronics Watts Industries Schneider Electric Johnson Controls Industrie Technik Oventrop Controlli Siemens Danfoss Frese Sauter Actuator codes Optima VA-7480-4001 VSX0xPB Compact VSXT0xPB VA-7480-4003 53-13xx (DN10-DN32) (DN10-DN32) VA-7481-4003 VSX03PB Optima Compact VSX04PB VA-7482-5001 53-13xx VSX05PB -----------------------2,5 mm VSX06PB (DN10-DN20) (DN10-DN20) Optima VSXT03PB Compact VSXT04PB VA-7482-6001 -------53-13xx -------___ ----____ -----------VSXT06PB 5.0 mm (DN10-DN20) (DN10-DN20) Optima Compact VSXT07PB VA-7482-7001 53-13xx VSX08PB 5,5 mm (DN25-DN32) (DN25-DN32) TBV-C (DN15-DN20) VUT Series VVP47 Series TBV-CM **BUT Series** VG3000 Series (DN15-DN25) COCON QTZ VXP47 Series (DN10-DN32) VXL Series V5000 Series VZx8 TBV-CMP VA-7482-8201 VMP47 Series 91 Series 2131 Series (discontinued) Series (DN15-DN25) VA-7482-8201-RA AB-QM VFX Series COCON 2TZ **BXL** Series 92 Series 3131 Series VVI46 Series VA-7482-8002-RA (DN10-DN32) (DN15-DN20) (DN15-DN20) VG6000 Series VZx8C KTCM512 VCL VA-7482-8302-RA VXI46 Series 93 Series 4131 Series (DN15-DN20) (discontinued) Tri-M Plus (DN10-DN32) (DN15-DN25) (DN15) VVS46 Series VP1000 Series TA Compact **VUL** Series (DN10-DN32) VXS46 Series **BUL Series** TA Modulator (DN15-DN20) Optima Compact VSX03PB 53-13xx VSX04PB 2,5 mm VSX05PB (DN10-DN20) VSX06PB (DN10-DN20) Optima VA-7482-9201 Compact VSXT03PB VA-7482-9201-RA 53-13xx -------VSXT04PB VA-7482-9002-RA 5.0 mm VSXT06PB (DN10-DN20) (DN10-DN20) Optima VSXT07PB Compact VSX08PB 53-13xx (DN25-DN32) 5,5 mm (DN25-DN32) TBV-C (DN15-DN20) VUT Series VVP47 Series TBV-CM **BUT Series** VG3000 Series (DN15-DN25) COCON QTZ VXP47 Series VA-7483-8201 (DN10-DN32) VXL Series V5000 Series VZx8 TBV-CMP VMP47 Series 91 Series 2131 Series VA-7483-8201-RA Series (DN15-DN25) (discontinued) COCON 2TZ **BXL** Series AB-QM VFX Series 92 Series 3131 Series VA-7484-8001 VVI46 Series ____ ----(DN10-DN32) (DN15-DN20) (DN15-DN20) VG6000 Series VZx8C KTCM512 VCI VA-7484-8001-RA VXI46 Series 93 Series 4131 Series (discontinued) (DN15-DN20) (DN15-DN25) Tri-M Plus (DN10-DN32) VVS46 Series (DN15) VP1000 Series TA Compact **VUL** Series (DN10-DN32) VXS46 Series BUI Series TA Modulator (DN15-DN20) Optima Compact VSX03PB 53-13xx VSX04PB 2,5 mm VSX05PB (DN10-DN20) VSX06PB VA-7483-9201 Optima (DN10-DN20) VA-7483-9201-RA Compact VSXT03PB VA-7484-9001 ----53-13xx ---VSXT04PB VA-7484-9001-RA 5.0 mm VSXT06PB (DN10-DN20) (DN10-DN20) Optima VSXT07PB Compact VSX08PB 53-13xx (DN25-DN32)

5,5 mm (DN25-DN32)

Operation

24 VAC Floating Model

When the signal is applied to the black and red wires, the actuator stem extends. When the signal is removed the actuator remains in position. If the signal remains applied to the red wire, the actuator will time out and shut off the motor after approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/ mm models).

When the signal is applied to the black and orange wires, the actuator stem retracts. When the signal is removed the actuator remains in position. If the signal remains applied to the orange wire, the actuator will time out and shut off the motor after approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models).

End of stroke confirmation

When the signal is applied in the same direction, the actuator turns on every 2 hours and drives in the signal direction for approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models) to confirm the end of stroke position.

Table 1: Actuator stem direction

Input		Direction
Red wire energised	↓	Actuator stem extends
Orange wire energised	↑	Actuator stem retracts

230 VAC Floating Model

When the signal is applied to the blue and brown wires, the actuator stem extends. When the signal is removed the actuator remains in position. If the signal remains applied to the brown wire, the actuator will time out and shut off the motor after approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models).

When the signal is applied to the blue and orange wires, the actuator stem retracts. When the signal is removed the actuator remains in position. If the signal remains applied to the orange wire, the actuator will time out and shut off the motor after approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models).

End of stroke confirmation

When the signal is applied continuously in the same direction, the actuator turns on every 2 hours and drives in the signal direction for approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models) to confirm the end of stroke position.

Table 2: Actuator stem direction

Input		Direction		
Brown wire energised	¥	Actuator stem extends		
Orange wire energised	↑	Actuator stem retracts		

24 VAC/VDC Proportional Model with fixed stroke

VA-7482-xx01 Factory Stroke configured series (jumper setting)

When the power is applied, the actuator self-calibrates performing an auto-zero detection cycle. The actuator moves the stem down for a complete mechanical valve stroke until no changes are detected. Once the auto-zero is detected the actuator moves the stem accordingly with the input signal, within the value of the electrical stroke as per jumper setting.

When the input signal increases (eg. from 0V to 10V) the actuator stem extends if the actuator is configured as Direct Action (DA) or retracts if the actuator is configured as Reverse Action (RA).

When the input signal decreases (eg. from 10V to 0V) the actuator stem retracts if the actuator is configured as Direct Action (DA) or extends if the actuator is configured as Reverse Action (RA) (see Table 3).

End of stroke confirmation

For VA-7482-0011 model only:

When the input signal is at 0 or 100%, the actuator turns on every 2 hours and drives in the signal direction for approximately 90 seconds (13 sec/mm models) and approximately 60 seconds (8 sec/mm models) to confirm the end of stroke position.

For VA-7482-xx01 models:

When the input signal is at 100% the actuator turns on every 2 hours and drives in the signal direction for approximately 60 seconds to confirm the end of stroke position.

Table 3: Actuator stem direction

Action	Input	Direction		
Direct ecting	0-10 VDC	≁	Actuator stem extends	
Direct acting	10-0 VDC	↑	Actuator stem retracts	
Deverse esting	0-10 VDC	↑	Actuator stem retracts	
Reverse acting	10-0 VDC	¥	Actuator stem extends	

24 VAC/VDC Proportional Model with auto stroke capability

VA-7482/3/4-8x01 and VA-7482/3/4-9x01 Auto Stroke detection series

IMPORTANT: Auto Stroke detection is suitable for valves with minimum 2 kg spring preloading.

When the power is applied, the actuator performs the auto stroke detection cycle to detect the real valve stroke. The actuator moves the stem down for a complete mechanical valve stroke until no stroke changes are detected. Once the lower valve stem position is detected, the actuator moves the spindle up until it is fully retracted while the microprocessor counts and stores the full stroke of the actuator. Then, the actuator drives the spindle down in order to detect the upper valve stem position, being able to calculate the real stroke subtracting the gap value. As soon as the spindle of the actuator touches the valve stem, the actuator stops the auto stroke detection cycle (red LED blinking) and starts the operational mode (green LED blinking).

When the input signal increases (eg. from 0V to 10V) the actuator stem extends if the actuator is configured as Direct Action (DA) or retracts if the actuator is configured as Reverse Action (RA).

When the input signal decreases (eg. from 10V to 0V) the actuator stem retracts if the actuator is configures as Direct Action (DA) or extends if the actuator is configured as Reverse Action (RA) (see *Table 4*).

Note: The actuator will perform the auto stroke detection cycle every time it is powered off/powered on.

End of stroke confirmation

For VA-7482-8x01 and VA-7482-9x01 models:

When the input signal drives the actuator to completely extend the spindle for 2 hours, the actuator turns on the motor and drives the spindle in accordance with the signal for approximately 60 sec. to confirm the end of the stroke position.

For VA-7483/4-8x01 and VA-7483/4-9x01 models:

When the input signal drives the actuator to completely extend the spindle for 2 hours, the actuator turns on the motor and drives the spindle back for a short distance and then towards the end-stroke until stall is detected to confirm the end of the stroke position.

Table 4: Actuator stem direction

Action	Input	Direction		
Direct acting	0-10 VDC	¥	Actuator stem extends	
Direct acting	10-0 VDC	↑	Actuator stem retracts	
Deveree estima	0-10 VDC	↑	Actuator stem retracts	
Reverse acting	10-0 VDC	≁	Actuator stem extends	

24 VAC/VDC Proportional Model with 0-10 VDC feedback output (VA-7483 and VA-7484)

Position feedback

The position feedback signal is for monitoring the actuator stroke position. It feeds information internally to the positioner and a 0-10 VDC signal can supply an external supervisory system. *See Table 5* for correspondence between control signal and feedback output.

Table 5: Positive feedback signal

	-
Input signal range	Feedback output range
0-10V	0-10V
2-10V	0-10V
0-20 mA	0-10V
4-20 mA	0-10V
Custom Range	0-10V

24 VAC/VDC Proportional Model with 0-10 VDC feedback output and electric fail safe (VA-7484)

Electrical fail safe

The actuator is equipped with a super capacitor, which, in case of power failure, will drive the actuator and valve to the pre-defined safety position either open or closed. When the power supply is restored, the actuator will be available for normal operation after the super capacitor is fully charged within 150 sec. After the super capacitor is charged a new auto stroke detection routine is performed.

The electrical safety technology has been designed for a long life service with 5000 full charges guaranteed.

Table 6: Electric fail safe direction

Setting		Direction		
EFSD (Electric Fail Safe Down)	¥	Actuator stem extends in case of power failure		
EFSU (Electric Fail Safe Up)	↑	Actuator stem retracts in case of power failure		

Operating status indication

24 VAC/230 VAC Floating Model

The floating models are equipped with a green LED which provides information about the operating status.

Table 7: LED status

OFF	0	No power supply	
Green blinking	\rightarrow	Moving to position	
Green blinking	\rightarrow	End stroke confirmation	
Green steady on	*	End stroke reached	

24 VAC/VDC Proportional Model

The proportional models are equipped with a bi-colour LED (green-red) which provides information about the operating status and diagnostics.

Table 8: LED status and diagnostics

OFF	\bigcirc	No power supply
Green blinking	\rightarrow	Moving to position
Green blinking	\rightarrow	End stroke confirmation
Green steady on		Position reached
Red blinking	\rightarrow	Cycle
Red steady on		4-20 mA or 2-10 VDC signal lost

24 VAC/VDC Proportional Model with feedback

The proportional models are equipped with a bi-colour LED (green-red) which provides information about the operating status and diagnostics.

Table 9: LED status and diagnostics

OFF	0	No power supply
Green blinking	\rightarrow	Moving to position
Green steady on		Position reached
Red blinking slow	\rightarrow	Initialization / Auto stroke detection
Red blinking fast	-	Sticking Error
Red steady on		4-20 mA or 2-10 VDC signal lost

24 VAC/VDC Proportional Model with feedback and electric fail safe

The proportional models are equipped with a RGB LED which provides information about the operating status and diagnostics.

Table 10: RGB status and diagnostics

OFF	0	No power supply		
RGB blinking		Not configured		
Green blinking	\rightarrow	Moving to position		
Green steady on	-)	Position reached		
Red blinking slow	\rightarrow	Initialization / Auto stroke detection		
Red blinking fast	-	Sticking error		
Red steady on		4-20 mA or 2-10 VDC signal lost		
Blue blinking slow	-	Super capacitor acting, Fail Safe on action		
Blue blinking fast	->	Super capacitor close to end of life. Recommended actuator replacement		
Blue steady on		Super capacitor recharging		

Mounting instructions

When mounting the actuator on terminal unit valves, follow these instructions:

- Never use the actuator as a mounting lever.
- It is recommended that the valves be mounted upright or at angles not greater than 90° in an easily accessible location.




Figure 2: Mounting position

- Do not mount the actuator upside down to avoid dripping water, as this could enter the housing and damage the mechanism or motor.
- · Do not cover with insulating material.
- Hand tighten only. Do not over tighten. When mounting the actuator on the valve, only hand tighten the brass threaded coupling. Using a wrench to tighten the coupling will damage the actuator, cause it to fail, and will void the warranty. Position the actuator on the valve before tightening by hand.




Figure 3: Hand tighten only

Johnson

ontrols

- Never grab the actuator and forcibly turn it. To reposition the actuator on the valve, loosen the coupling, reposition the actuator and then retighten the brass coupling by hand.
- Sufficient clearance must be allowed for actuator removal (see dimensions below).




Figure 4: Clearance

• Check to be sure the actuator spindle is in its full retracted position as received.



Figure 5: Spindle retracted

• Do not connect the power supply before mounting the actuator on the valve.

Removing actuator from valve

IMPORTANT: Do not remove the actuator without switching off its power supply

In some situations, you may need to mount the actuator to a new valve with different closing dimensions. For example, if a Pressure Independent Control Valve (PICV) needs to be repositioned with a new stroke setting to suit new flow requirements, or a new valve with different closing dimensions replaces the old one. To safely mount the actuator to the new valve, complete the following steps:

24VAC & 230 VAC Floating models, VA-7482-xx01 Factory Stroke configured Series (Jumper setting) and VA-7482/3-8x01 and VA-7482/3-9x01 Auto Stroke detection series:

- Set the input signal to the actuator, to move the valve stem to the max extended position (the actuator spindle will move to the retracted position)
- 2. Switch off the power supply on the actuator
- 3. Remove the actuator
- 4. Check that the actuator spindle is in the retracted position (see Figure 5, further details on page 10)



Figure 6: Spindle retracted

- 5. Set the new valve position (for PICV) or replace by the new valve
- 6. Refit the actuator to valve
- 7. Switch on the power supply on the actuator
- 8. The actuator will perform the standard or auto stroke detection cycle again to reposition itself based on the new valve setting.

VA-7484-8x01 and VA-7484-9x01 Auto Stroke detection series:

If the actuator is set to Electrical Fail Safe Up :

- Set the input signal to the actuator, to move the valve stem to the max extended position (the actuator spindle will move to the retracted position)
- 2. Switch off the power supply on the actuator
- 3. Remove the actuator

 Check that the actuator spindle is in the retracted position (see Figure 6, further details on page 10)



Figure 7: Spindle retracted

- 5. Set the new valve position (for PICV)
- 6. Refit the actuator to valve
- 7. Switch on the power supply on the actuator
- 8. The actuator will perform the auto stroke detection cycle again to re-position itself based on the new valve setting.

If the actuator is set to Electrical Fail Safe Down:

- 1. Set the input signal to the actuator, to move the valve stem to the max extended position (the actuator spindle will move to the retracted position)
- 2. Switch off the power supply on the actuator
- 3. Connect the configuration tool to the actuator and select **Safe Unmounting** option
- 4. Remove the actuator
- 5. Check that the actuator spindle is in the retracted position (see Figure 7 below, further details on page 10)



Figure 8: Spindle retracted

- 4. Set the new valve position (for PICV) or replace by the new valve
- 5. Refit the actuator to valve
- 6. Switch on the power supply on the actuator
- 7. The actuator will perform the auto stroke detection cycle again to reposition itself based on the new valve setting.

Wiring instructions



WARNING

When servicing make sure that:

- the electric supply to the actuator is switched off to avoid possible damage to the equipment, personal injury or shock.
- you do not touch or attempt to connect or disconnect wires when electric power is on.
- all wiring should conform to local codes and must be carried out by authorized personnel only.
- keep high and low voltage wiring separated.
- when using multi-stranded wire apply a cable ferrule to the cable end.
- make sure that the line power supply is in accordance with the power supply specified on the device.
- check all wiring connections before applying power to the system.

Contact with components carrying hazardous voltage can cause electric shock and may result in severe injury or death.

Short-circuited or improper connected wires may result in permanent damage to the equipment. Not adhering to these operational instructions could cause injury or damage the equipment.

Wiring Diagrams




Figure 9: 24 VAC Floating Model




Figure 11: 24 VAC/VDC Proportional Model




Figure 10: 230 VAC Floating Model




Figure 12: 24 VAC/VDC Proportional Model with feedback and Proportional Model with feedback and electric fail safe

Dip switch settings (Proportional Models only)

VA-7482 Models

These proportional models have a 6 dip switches which allow the user to field configure the actuator. The actuator is factory released with all the dip switches in OFF position.




Figure 13: VA-7482 dip switches

VA-7483 Models

These proportional models have 8 dip switches which allow the user to field configure the actuator.

The actuator is factory released with all the dip switches in OFF position.

DIP SV	WITCH OPTIONS 위 오
05VDC	510VDC 510VDC 210VDC 420MA
DA DA	∎ RA Þ
	🗖 Eq% ு
UDC	n mA o
□ NOT USED	NOT USED 🖓
□ NOT USED	■ NOT USED ∞
1: 2: CONTROL SIG 3: RANGE	SNAL 5: CURVE 6: SIGNAL TYPE 7: NOT USED
4: ACTION	8: NOT USED

Figure 14: VA-7483 dip switches

Dip switch 1, 2, 3, 6

The dip switches 1, 2, and 3 allow the user to change the analog input ranges. To switch from voltage analog input to current analog input the dip switch 6 has to be set accordingly.

Dip switch 4

The dip switch 4 allows the user to change the action of the actuator in relation of the analog input.




Figure 15: The dip switch 4 OFF (Direct Acting – DA) When the signal increases the actuator stem extends.




Figure 16: The dip switch 4 ON (Reversing Acting – RA) When the signal increases the actuator stem retracts.

Dip switch 5

Use the dip switch 5 to change the control characteristics of the actuator in order to obtain a combination of valve and actuator linear or almost equal percentage.

Dip switch 5 OFF (linear)

Use this option with linear or equal percentage control valves.

Dip switch 5 ON (almost equal percentage)

Use this option with quick opening or on/off control valves.

Configuration tool (VA-748X-CONF)

VA-7484 Models

The user can field configure these proportional model actuators through an external user-friendly configuration tool (VA-748X-CONF). The actuator is released with the below factory settings (factory settings in **bold**).

FAC SET	44			
Y(+) [***] Analog Input	0-10 VDC 2-10 VDC 0-5 VDC 5-10 VDC	0-20 mA 4-20 mA		
Action	DA	RA		
Curve	LIN	Eq%		
Fail Safe Action	EFSD (Electrical Fail Safe Down)	EFSU (Electrical Fail Safe Up)		

Follow these steps to connect the configurator tool to the actuator:




Figure 17: Configurator connection instructions

Power-on

To power on, connect the configuration tool to the actuator's dedicated port and press the encoder button for more than 2 seconds.

Note: The configuration tool will automatically power off after a few seconds if it does not detect any connected actuator.

Configuration process

Use the rotary encoder to navigate through the menu. Rotate clockwise to show the next item on the display, and counterclockwise to show the previous one.

To select an item, press the encoder button for more than 2 seconds. To return to the previous level menu, press the encoder button for more than 4 seconds.

The first-level menu contains the following options:

- 1. Load Configuration: Shows the last saved configuration on the display and uploads it into the actuator
- 2. Set Configuration: Shows all configurable parameters
- 3. **Safe Unmounting:** Select this option to remove the actuator safely from the valve. The actuator will fully retract the spindle.




Figure 18: Configuration tool

Table 17: Configuration tool

Callout	Component
A	LED status
В	Display
С	Rotary Encoder button

Set Configuration process

When option **Set Configuration** is selected, all configurable parameters are shown. Select a specific parameter to go through the different available parameter values.

After selecting a new parameter value the configuration tool will automatically go back to the parameter list. In order to go back to the parameter list without changing the current value press the encoder button for more than 4 seconds. The parameters and their values are as below:

- 1. Control signal type
 - a. Voltage
 - b. Current

2. Control signal span

- a. 0-10V (if "Voltage" setting chosen)
- b. 2-10V (if "Voltage" setting chosen
- c. 0-5V (if "Voltage" setting chosen)
- d. 5-10V (if "Voltage" setting chosen)
- e. 0-20 mA (if "Current" setting chosen)
- f. 4-20 mA (if "Current" setting chosen)

3. Action type

- a. DA (Direct Action)
- b. RA (Reverse Action)

4. Curve type

- a. Linear
- b. EQ%

5. Fail Safe action

- a. Electrical Fail Safe Up
- b. Electrical Fail Safe Down
- 6. Save Configuration
 - a. Yes
 - b. No
- 7. Load Configuration

Safe unmounting procedure

To safely remove the actuator from the valve when it is set with Electrical Fail Safe Down (EFSD) configuration, complete the following step.

Note: The configuration tool must be connected to the actuator following the dedicated procedure.

In the first level menu choose the **Safe Unmounting** option. This will cause the actuator to fully retract the spindle, allowing the safe removal of the actuator from the valve. When performing this operation the actuator's settings will not be changed.

WARNING: Do not remove an actuator with Electrical Fail Safe Down (EFSD) configuration from valve without performing the safe unmounting procedure.



Electrical actuator stroke and closing dimensions

All the Proportional models with factory stroke configuration option have 1 jumper with which the user can change the electrical stroke.

The actuators are delivered with the following factory settings (*see table below*). **Note:** All Proportional models with Auto stroke detection do not require the jumper as they can detect the real valve stroke automatically.

All the Floating models have fixed stroke and the jumper option is not available.




Figure 19: Stroke options

				Figure 19: Stroke options				
UMES LLMES	Ĩ		Product codes	Note				
	PDTC O PDTC PDTO			Proportional model VA-7482-0011 (suitable for the VG5000 and VG4000) For proportional actuator, suitable for the VG5000 or VG4000, the jumper allows the user to set push down to close (PDTC) or push down to open (PDTO) function. The actuator is factory set for use with 2-way Push Down to Close (PDTC) VG4200 and VG5200 valves. For 2-way Push Down To Open (PDTO) VG4400 and VG5400 valve applications set the valve port selection jumper to PDTO. For 3-way VG4800 and VG5800 valve applications set the jumper to the valve port type that corresponds to the service port of the valve.				
			VA-7482-0011					
		3.2 mm	VA-7482-1x01					
LMES 10.0 mm		4.3 mm	VA-7482-2x01					
		6.0 mm	VA-7482-3x01					
	Auto Stroke Detection		VA-7482-8x01					
			VA-7482-8002-RA					
			VA-7483-8201	Proportional model VA-7482-x001 / VA-7482-8x01 / VA-7482-9x01 /				
			VA-7484-8001	VA-7483-8201 / VA-7483-9201 / VA-7484-8001 / VA-7484-9001 The proportional actuator VA-7482-x001 series is suitable for different terminal units				
		2.5 mm	VA-7482-5x01	in the market as shown on the <i>Valve compatibility</i> table, pages 4 and 5.				
		5 mm	VA-7482-6x01					
UMES 14.5 mm		5.5 mm	VA-7482-7x01					
LMES 8.2 mm	Auto Stroke Detection		VA-7482-9x01					
			VA-7482-9002-RA					
			VA-7483-9201					
			VA-7484-9001					
UMES 16.3 mm LMES 10.0 mm			VA-7480-0xxx VA-7481-0xxx	Floating model VA-7480-0xxx / VA-7481-0xxx / VA-7480-4xxx / VA-7481-4003				
UMES 14.5 mm LMES 8.2 mm			VA-7480-4xxx VA-7481-4003	All the floating models have fixed stroke and the jumper option is not available.				

Note: UMES: Upper Mechanical End Stroke / LMES: Lower Mechanical End Stroke



Dimensions






Figure 20: Actuator dimensions

Technical specifications

Actuator models	VA-7480-x0x1	VA-7481-00x1	VA-7481-x0x3	VA-7481-x0x3	VA-7482-x002-RA	VA-7482-x0x1	VA-7483-x201	VA-7484-x00	
Action control	Floating or PAT					Proportio	nal		
Supply voltage (50/60Hz)	24 VAC ±15% 230 VAC ±10%				24 VAC ±1 24 VDC ±1				
Feedback									
Signal					0-10 VDC ±5%				
Rating						max 2 mA at 0-10 VDC			
Input impedance									
Voltage		-				>100 kG	2		
Current		-	-			500 Ω			
Power consumption									
Apparent (Running)	2.5	2.5 VA 6.0 VA				2.5 VA			
Active (Running)	1.5	1.5 W 2.2 W				1.5 W			
Apparent (Charging)								5 VA	
Active (Charging)								3W	
Max stroke		6 mm							
Running time	13 sec/mm	8 sec/mm	13 sec/mm		8	3 sec/mm			
Charging time								150 sec	
Protection	IP	54	IP	43		IP54			
Material									
Cover				ABS	+ PC				
Yoke			PA6	6 – Glass Mine	eral filled (30% total))			
Thread nut		Brass CuZn40Pb2							
Housing colour				White sem	itransparent				
Thread nut connection		See "Ordering Codes"							
Ambient operating condition		0°C to 50°C, 10 to 90 RH%							
Ambient storage condition		-20°C to 65°C, 5 to 95 RH%							
Max. fluid temperature				95	°C				
Electrical connections		ble length 35 mm²)		ble length 75 mm²)	1.5m CMP	1.5 m cable length (3 x 0.35 mm ²)	2 m cable length (4 x 0.35 mm ²)	1.5 m cable length (4 : 0.35 mm2	
Operating status indica- tions	LED								
Audible noise rating	< 30 dB(A)								
Life	250,000 cycles (standard models) / 150.000 cycles (auto stroke models)								
Shipping weight	0.2 Kg								
C C Compliance	Johnson Controls declares that this product is in compliance with the essential requirements and other relevant provisions of the EMC Directive and Low Voltage Directive. , VA-7482-x002-RA Is Tested per UL2043. Suitable for Use in Other Environmental Air Space (Plenums) in Accordance with Section 300.22 (C) of the National Electrical Code. UL 60730-1 Listed Type 2 Enclosure, File E194024 XAPX XAPX7								

Single point of contact

APAC

JOHNSON CONTROLS C/O CONTROLS PRODUCT MANAGEMENT NO. 32 CHANGJIJANG RD NEW DISTRICT WUXI JIANGSU PROVINCE 214028 - CHINA

Europe

JOHNSON CONTROLS WESTENDHOF 3 45143 ESSEN GERMANY

NA/SA

JOHNSON CONTROLS 507 E MICHIGAN ST MILWAUKEE WI 53202 USA

Contact information

Contact your local branch office: <u>www.johnsoncontrols.com/locations</u> Contact Johnson Controls: <u>www.johnsoncontrols.com/contact-us</u>



Building Technologies & Solutions Headquarters: Milwaukee, Wisconsin, USA Branch Offices: Principal Cities World-wide © Copyright 2021 Johnson Controls. All specifications and other information shown were current as of document revision and are subject to change without notice.